

## Features

- All-purpose tool that can be used as both shears ( $\varnothing$  1.3mm – 16 awg) and wire strippers with fixed hole ( $\varnothing$  0.4mm – 26 awg).
- Steel thickness 3mm.
- ESD-safe.
- Ergonomi anti-slip bi-component handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- Laser marking.
- Made in Italy.

## RS PRO ESD Shears ( $\varnothing$ 1.3mm-16 awg) and Wire Stripper ( $\varnothing$ 0.4mm-26 awg)

RS Stock No.: 0715755



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO ESD Shear and Wire Strippers

RS PRO ESD All-purpose tool that can be used as both shear ( $\varnothing$  1.30mm - 16 awg) and wire stripper ( $\varnothing$  0.4mm - 26 awg).

Steel thickness 3mm. Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.

ESD-safe version. Made with high carbon steel and undergo a controlled atmosphere heat treatment. The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.

## General Specifications

<b>Cutter Type</b>	Shear and wire stripper
<b>Materials Cut</b>	$\varnothing$ 1.3mm (16 awg) for shears $\varnothing$ 0.4mm (26 awg) for wire strippers (fixed hole)
<b>No Sparking</b>	No
<b>Overall Length</b>	144mm +/- 2mm
<b>VDE/1000V Approved</b>	No
<b>Height Safe</b>	No
<b>ESD Safe</b>	Yes
<b>Material</b>	High Carbon Steel
<b>Maximum Cutting Capacity</b>	1.30mm

## Approvals

<b>Declarations</b>	REACH DoC
<b>Standards Met</b>	IEC 61340-5-1 (ESD)

