

Durable chemical-resistant gloves with heightened grip, ideal for outdoor application

- **Enhanced grip:** AlphaTec® 58-530B chemical gloves' ANSELL GRIP™ coating means less force is needed for handling wet or oily parts
- **Elevated comfort:** Their black acrylic inner liner enhances comfort while facilitating outdoor application
- **Advanced defenses:** These AlphaTec® gloves' bonded construction, with a coating polymer that doesn't penetrate the liner in manufacture, ensures EN 374 Type A chemical protection
- **Improved durability:** They also achieve ANSI/ISEA 105-2024 ABRASION LEVEL 5 and EN ABRASION LEVEL 3
- **Specialized protection:** Beyond chemical protection, they possess EN 407 contact heat level 1, preventing workplace injuries
- **Augmented dexterity:** AlphaTec® 58-530B PPE gloves' light 7-gauge design makes them more dexterous, for maneuverable hand protection



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Food Processing

Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Changing tools and dies
- Handling application & cleaning tools
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Food Processing

Key Features

- **ANSELL GRIP™ Technology:** Less force needed to grip wet or oily parts
- **Black acrylic liner:** Comfortable and ideally colored for outdoor usage
- **Bonded construction:** No liner penetration and heightened dexterity

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



Performance Standards

ANSI/ISEA 105-2024



EN388: 2016



3122A

EN 407



XIXXXX

EN ISO 374-1:2016



AJKLOPT

EN ISO 374-5:2016



0493

Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 58-530B	Liner Material: Acrylic Coating Material: Nitrile Featured Technology: ANSELL GRIP™	7	7, 8, 9, 10, 11	290 / 11.4	Grey	6 pairs/polybag; 12 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Bldv. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.