



Angle Grinder XGT® 230 mm

GA038G

40V max • 230 mm • 6 600 min⁻¹

Efficient brushless tool for cutting and grinding.

Brushless, paddle switch angle grinder with a 230 mm wheel for demanding professional use. Adjustable speed from 6 600 min⁻¹ by using variable speed control dial. AWS remote vacuum cleaner start function.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	6600 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	230 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	98 dB(A)
Sound Pressure Level (L _{pA})	90 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	4,6 - 8,2 kg
Product Dimensions (L x W x H):	516 x 250 x 176 mm

User benefits

- Outperforming performance and efficiency similar to corded 1 000 W class grinder
- Genuine solution for high demand industrial applications
- Excellent in continuous heavy-duty work
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Anti-restart function minimises accidental start-up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low
- Soft start for smooth start-ups

Link to product - www.makitauk.com



Related products

Optional AC

122913-6

Wheel Cover 230mm



143486-6

Grip 37



195385-8

Dust collecting cover 180 mm, Ø



198440-5

Dust collecting cover 230 mm, Ø



782034-2

Lock Nut Wrench 35



821841-9

Carrying case



Other

[User manual](#)

[Parts drawing](#)