

## **FEATURES**

- 2m lead and 13A fused Moulded plug
- 4 or 6 socket versions
- Type G- British socket type
- Integral fuse carrier supplied with a 7A BS1362 fuse, for compliance with BS6396 'Office Equipment Standard'

# RS PRO 2m 4 Socket Type G - British Trailing Socket, 230 V ac

RS Stock No.: 374-216



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

RS PRO range of trailing extension sockets styled in grey to suit modern office environments. All models come with a 2 m lead and are highly reliable and excellent quality.

Extension leads are extremely useful and can be used for a range of applications at home or in the office or workplace, from powering electronic equipment like printers and PCs, as well as powering multiple industrial machines or appliances.

#### Options include:

- 455-264 4-way standard trailing socket, voltage rating 230 V ac
- 455-286 6-way standard trailing socket, voltage rating 250 V ac
- 249-4536 4-way surge protected trailing socket, 4.5kA, voltage rating 250 V ac
- 249-4558 6-way surge protected trailing socket,4.5kA, voltage rating 230 V ac
- 249-4564 4-way surge and noise protected trailing socket, voltage rating 230 V ac
- 249-4592 6-way surge and noise protected trailing socket, voltage rating 230 V ac
- 206-7500 2-way surge and filtered trailing socket, 6.5kA, voltage rating 230 V ac
- 455-321 4-way surge and filtered trailing socket,6.5kA, voltage rating 230 V ac
- 455-343 6-way surge and filtered trailing socket,6.5kA, voltage rating 230 V ac
- 374-216 4-way surge filtered and RCD trailing socket, voltage rating 230 V ac

#### **General Specifications**

Туре	Socket Strip
Colour	Grey
Number of Sockets	4
Surge Protection	Yes
Switchable	Yes
RCD Protected	Yes
Response Time	<10ns
Overload protection	Yes
Application	Mobile phone chargers, including those with a USB connectivity, Household entertainment (TVs, satellite boxes, routers etc.), Industrial machines and equipment, Office desks (Monitors, computers, phones), Any electrical device needed to be powered by the mains



# **Electrical Specifications**

Socket Type	Type G - British
Voltage Rating	230V ac
Current Rating (Unwound)	13A
Frequency	50/60Hz
Surge Handling (8/20µs)	19.5kA [6.5kA]
Voltage Protection Level (Up) 8/20µs	900V@3kA 8/20μs

## **Mechanical Specifications**

Cable Length	2m
--------------	----

# **Approvals**

Compliance/Certifications	EN61340
Standards Met	BS EN61643-11/12 - Type III, Class III