

Features

- High precision strain gauge loadcell
- Accuracy: 1 part in 30,000.
Internal resolution: 1 part in 600,000
- High quality re-chargeable battery, for long operating time
- Stainless steel platform cover- virtually impervious to harsh chemicals
- Rugged, die cast sub-platform to facilitate stable display.
- RS232 interface port

RS PRO Counting Weighing Scale, 30kg Weight Capacity

RS Stock No.: 0212398, 0212399, 0212400, 0212401, 0212403



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Platform Weighing Scale

RS PRO professional counting weighing scale ideal for strong, sturdy daily weighing applications.

- Accuracy: 1 part in 30,000.
Internal resolution: 1 part in 600,000
- High precision strain gauge loadcell
- High quality re-chargeable battery for long operating time.
- Stainless steel platform cover- virtually impervious to harsh chemicals
- Rugged, die cast sub-platform to facilitate stable display.
- RS232 interface port

General Specifications

Weighing Capacity	30kg
Scale Type	Counting
Resolution	1g
Plug Type	Type A - North American/Japanese 2-blade, Type C - European Plug, Type G - British 3-pin, Type I - Australian plug
Weighpan Length	290mm
Weighpan Width	240mm
Net Weight	4.0kg
Minimum Operating Temperature	0°C
Maximum Operating Temperature	40°C
Power Requirement	Adapter and Rechargeable Battery (included)

Approvals

Certification	CE
Declarations	REACH DoC