

BK-4HCDE CASE

eneloop pro AAA — Case Pack



Key Specifications

Parameter	Value
Part Number	BK-4HCDE CASE
Cell size	AAA (Micro)
Chemistry	Ni-MH, LSD, high-capacity 'pro' line
Nominal voltage	1.2 V
Capacity (typ. / min.)	950 mAh / 930 mAh
Rechargeable cycles	Up to 500 times
Charge retention	70% after 5 years storage
Weight	≈13 g per cell
Operating temperature	-20°C to 50°C (discharge)
Pack type	Bulk/case carton — multiple retail 4-packs per case