

Features

- High efficient heatsink
- Built-in gas release vent
- Screw fastener for safety precautions
- Drop resistance of 1 metre

RS PRO ATEX LED Torch Yellow 133lm, 174mm

RS Stock No.: 0145618



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO ATEX intrinsically safe LED torch

From RS PRO, comes a high quality and great value ATEX intrinsically safe LED torch. Manufactured with a tough and during casing and fitted with a CREE LED, this portable, handheld flashlight is an essential solution for use in hazardous locations

Features and benefits:

- The LED can operate at 133 LM (lumens) at the high setting and 32 LM at low
- High efficient heatsink and Built-in gas release vent
- The LED torch has high and low operating modes that allow users to operate for high brightness or long-duration lighting
- Screw fastener for safety precautions
- Drop resistance of 1 metre
- ATEX certified which is protection against explosive atmospheres
- Beam distance of 231m on the high mode and 110m on the low mode
- Powered by 4xAA alkaline or NiMH batteries

General Specifications

Torch Style	Straight
Rechargeable	No
Lamp Type	LED
Luminosity	133lm (high)/ 32lm (low)
Batteries	4 x AA
Case Material	Anti static plastic
Hazardous Area Certification	ATEX
Hazardous Area	Yes
Zone	Zone 0
Range	172M
Beam Type	Spot
Length	174mm
Colour	Yellow
Weight with Batteries	115g

Modes Specifications

Parameters	High Mode	Low Mode / Strobe
Light Output	133lm	32lm
Run Time	6 hours	69 hours
Beam Distance	231m	110m
Switching Modes	Hight/Low/Off	
Light Colour	White	
Anti-Corrosive	Yes	
Drop Resistance	1m	

Electrical Specifications

Rechargeable	No
Batteries	4 x AA alkaline battery (excluded)
Battery Indicator	No
Switch Type	Button switch






Mechanical Specifications

Length	174mm
Width	47 mm
Depth	47 mm
Weight (with Batteries)	115g

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE / UL / ATEX / IECE /
Standards Met	<div>  <p>Class I Div 1 Grp ABCD / Class II Div 1 Grp EFG Class III / Temperature Code T4 IP6X File number: E324236</p> </div> <div>  <p>II 1G Ex ia IIC T4 Ga I M1 Ex ia I Ma UL 23 ATEX 2997X UL23UKEX2856X</p> </div> <div>  <p>Ex ia IIC T4 Ga Ex ia I Ma IECEX UL 23.0029X</p> </div> <div>  <p>0518</p> </div> <div>  <p>2813</p> </div>
Hazardous Area Certification	ATEX; IECEX

Similar Products

Stock No.	Brand	Product Name	Luminosity	Batteries	Colour
0145616	RS PRO	ATEX Torch	180 lm (high)/ 70lm (low)	4 x AA	Yellow
0145619	RS PRO	ATEX Head Torch	200lm (high)/ 100lm (low)	3 x AAA	Yellow
0145618	RS PRO	ATEX Torch	133lm (high)/ 32lm (low)	4 x AA	Yellow