

FLAT-PACK TROLLEYS



250 KG

Trolleys with folding backrests

Designed for intensive use, it adapts to any environment. Its folding backrest makes it easy to store.


- Robust design with 35 x 20 mm tubular frame and under-tray reinforcements. Recessed top.
- Ergonomically designed handle in 28 mm Ø tube for a good grip. When folded, its shape allows the backrest to be raised without having to bend down too far.
- Protective tips at the front of the platter to prevent injury or damage to walls.
- Support bar to prevent loads from tipping over.
- Melamine top: 16 mm thick, suitable for carrying loads and easy to clean.
- Rubber wheels for smooth floors, 2 fixed + 2 swivel with brakes, EN 1757 standard.
- Delivered unassembled with cardboard packaging or assembled.



804 721 111



804 722 111



Product number delivered unassembled	Product number delivered assembled	Tray dimensions	Overall dimensions	Height from platform to floor	Height of folded backrest to floor	Ø Wheels	Bandage	Weight kg
804 721 111	806 721 111	S: 850 x 495	1105 x 540 x 945	195	375	125	CC	18.5
804 722 111	806 722 111	M : 1000 x 595	1255 x 640 x 945					21.5

CC : rubber / All our dimensions are given in mm

ZOOM



Protective tips at the front of the platter to prevent injury or damage to walls.



Backrest folding system.

OPTIONS



Reel
882 006 152
For rolls Ø 300 mm max.



A4 portrait document holder
882 006 150



Showerhead holder
882 006 149

RANGE VARIATIONS



Galvanised sheet
metal top



Medium tray



TPE wheels



Fixed backrest