

# PRODUCT SHEET

## 191-...A


### Mat chrome-plated 90° elbowed nose inner circlips pliers

Steel with chrome-vanadium.

The choice of the pattern is executed functions of the circlip diameter.

The nose form maintain perfectly the circlip during its use.

Presentation: Polish chromed finishing, PVC sheath branches.




reference	nozzle diameter mm	mini. Capacity mm	max. capacity mm	L mm	L"	Weight g
191-10A		8	13	139	5	55
191-13A		12	25	140	5	55
191-17A		19	60	180	7	100
191-21A		40	100	225	9	150
191-28A		85	140	310		440