

Main

Range	Actassi
Product or component type	Multimode fibre optic pigtail
Colour	Sheath: aqua LC housing: aqua LC boot: white
Cable packaging	Roll of 1 m
Type of packing	Plastic bag





Complementary

Maximum attenuation	3.5 DB / 1 km at 850 nm 1.5 dB / 1 km at 1300 nm
Bending radius	50 mm dynamic 30 mm static
Maximum insertion loss	0.2 dB LC
Minimum return loss	30 dB LC
Fibre performance	OM3 50/125 µm
Optic fiber diameter	900 µm
Exchange mode	Simplex
Mode of transmission	Multi mode
Number of optic fibre	1
Cable outer diameter	0.9 mm +/- 0.2 mm
Material	Ceramic: LC connector ferrule
Cable length	1 m
Targeted region	Europe Asia Pacific.

Environment

Ambient air temperature for operation	-20...60 °C
Ambient air temperature for installation	-20...60 °C
Ambient air temperature for storage	-20...60 °C
Standards	LC connector: TIA/EIA-604-10 A LC connector: IEC 61754-20 Ed.2 Fibre performance: ISO/IEC 11801:2011 Ed.2.2 OM3 Fibre performance: IEC 60793-2-10 Type A1a.2 Fibre performance: TIA/EIA-568-C.3 Fibre performance: ITU G.651 IEC 60754-1 IEC 60754-2 IEC 61034 Flame retardance: IEC 60332-1 Fire retardance: IEC 60332-3C Flame retardance: UL 94 V0

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Circularity Profile	No need of specific recycling operations