

# LONG LIFE SANDING WOOD AND PAINT

PRO

- 1 Tear-resistant X-cloth backing
- 2 Extra strong belt joint for roughest challenges



**BOSCH**

## PRO X440 SANDING BELT

**PRO**


- ▶ For sanding wood and paint, eg when sanding old paint and floor lacquer or finishing hardwood floors
- ▶ Highly efficient for painters: Long Life
- ▶ Designed for sanding wood and paint



PRODUCT PROPERTIES			ORDERING INFORMATION				Part number
Belt dimensions, width mm	Belt dimensions, length mm	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	
40	305	40	C1e	3	2	188 562	2 608 606 929
40	305	40	P0b	10	1	699 716	2 608 608 L87
40	305	60	C1e	3	4	165 426	2 608 606 206
40	305	60	P0b	10	1	699 723	2 608 608 L88
40	305	80	C1e	3	4	165 433	2 608 606 207
40	305	80	P0b	10	1	699 730	2 608 608 L89
40	305	120	C1e	3	4	165 440	2 608 606 208
40	305	120	P0b	10	1	699 747	2 608 608 L90
40	305	180	C1e	3	4	165 457	2 608 606 209
60	400	40	C1e	3	2	163 361	2 608 606 000
60	400	40	P0f	10	2	699 754	2 608 608 L91
60	400	60	C1e	3	4	163 378	2 608 606 001
60	400	60	P0f	10	4	699 761	2 608 608 L92
60	400	80	C1e	3	4	163 385	2 608 606 002
60	400	80	P0f	10	4	699 778	2 608 608 L93
60	400	100	C1e	3	4	163 392	2 608 606 003
60	400	100	P0f	10	4	699 785	2 608 608 L94
60	400	150	C1e	3	4	163 408	2 608 606 004
60	400	240	C1e	3	4	163 415	2 608 606 005
65	410	40	C1e	3	2	163 514	2 608 606 015
65	410	60	C1e	3	4	163 521	2 608 606 016
65	410	80	C1e	3	4	163 538	2 608 606 017
65	410	100	C1e	3	4	163 545	2 608 606 018
65	410	120	C1e	3	4	163 552	2 608 606 019
65	410	150	C1e	3	4	163 569	2 608 606 020
65	410	180	C1e	3	4	163 576	2 608 606 021
65	410	220	C1e	3	4	163 583	2 608 606 022
75	457	40	C1e	3	2	163 682	2 608 606 032
75	457	40	P0f	10	2	699 839	2 608 608 L99
75	457	40	P0f	10	2	711 142	2 608 608 M99
75	457	60	C1e	3	4	163 699	2 608 606 033
75	457	60	P0f	10	4	699 846	2 608 608 M00
75	457	80	C1e	3	4	163 705	2 608 606 034
75	457	80	P0f	10	4	699 853	2 608 608 M01
75	457	100	C1e	3	4	163 712	2 608 606 035
75	457	120	C1e	3	4	163 729	2 608 606 036
75	457	120	P0f	10	4	699 860	2 608 608 M02


**BOSCH**

## PRO X440 SANDING BELT

PRO

PRODUCT PROPERTIES			ORDERING INFORMATION				Part number
Belt dimensions, width mm	Belt dimensions, length mm	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	
75	457	150	C1e	3	4	163 736	2 608 606 037
75	457	180	C1e	3	4	163 743	2 608 606 038
75	457	220	C1e	3	4	163 750	2 608 606 039
75	480	40	C1e	3	2	163 781	2 608 606 042
75	480	60	C1e	3	4	163 798	2 608 606 043
75	480	80	C1e	3	4	163 804	2 608 606 044
75	480	100	C1e	3	4	163 811	2 608 606 045
75	480	120	C1e	3	4	163 828	2 608 606 046
75	480	150	C1e	3	4	163 835	2 608 606 047
75	480	180	C1e	3	4	163 842	2 608 606 048
75	480	220	C1e	3	4	163 859	2 608 606 049
75	508	40	C1e	3	2	163 965	2 608 606 060
75	508	40	P0f	10	4	699 877	2 608 608 M03
75	508	60	C1e	3	4	163 972	2 608 606 061
75	508	80	C1e	3	4	163 989	2 608 606 062
75	508	100	C1e	3	4	163 996	2 608 606 063
75	508	120	C1e	3	4	164 009	2 608 606 064
75	508	150	C1e	3	4	164 016	2 608 606 065
75	508	180	C1e	4	4	164 023	2 608 606 066
75	508	220	C1e	3	4	164 030	2 608 606 067
75	533	40	C1e	3	2	164 054	2 608 606 069
75	533	40	P0n	10	2	164 160	2 608 606 080
75	533	40	P0f	10	2	699 914	2 608 608 M07
75	533	60	C1e	3	4	164 061	2 608 606 070
75	533	60	P0n	10	1	164 177	2 608 606 081
75	533	60	P0f	10	4	699 921	2 608 608 M08
75	533	80	C1e	3	4	164 078	2 608 606 071
75	533	80	P0n	10	1	164 184	2 608 606 082
75	533	80	P0f	10	4	699 938	2 608 608 M09
75	533	100	C1e	3	4	164 085	2 608 606 072
75	533	100	P0n	10	1	164 191	2 608 606 083
75	533	120	C1e	3	4	247 955	2 608 607 258
75	533	120	P0n	10	1	247 962	2 608 607 259
75	533	120	P0f	10	4	699 945	2 608 608 M10
75	533	150	C1e	3	4	164 092	2 608 606 073
75	533	150	P0n	10	1	164 207	2 608 606 084
75	533	180	C1e	3	4	247 979	2 608 607 260
75	533	180	P0n	10	1	247 986	2 608 607 261
75	533	220	C1e	3	4	164 108	2 608 606 074
75	533	220	P0n	10	1	164 214	2 608 606 085
75	610	40	C1e	3	2	164 252	2 608 606 089
75	610	60	C1e	3	4	164 269	2 608 606 090
75	610	80	C1e	3	4	164 276	2 608 606 091
75	610	100	C1e	3	4	164 283	2 608 606 092
75	610	120	C1e	3	4	164 290	2 608 606 093
75	610	150	C1e	3	4	164 306	2 608 606 094
100	552	40	C1e	3	2	164 979	2 608 606 161
100	552	60	C1e	3	4	164 986	2 608 606 162


**BOSCH**

## PRO X440 SANDING BELT

PRO

PRODUCT PROPERTIES			ORDERING INFORMATION				Part number
Belt dimensions, width mm	Belt dimensions, length mm	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	
100	552	80	C1e	3	4	164 993	2 608 606 163
100	552	100	C1e	3	4	165 006	2 608 606 164
100	552	120	C1e	3	4	165 013	2 608 606 165
100	552	150	C1e	3	4	165 020	2 608 606 166
100	560	40	C1e	3	2	164 498	2 608 606 113
100	560	60	C1e	3	4	164 504	2 608 606 114
100	560	80	C1e	3	4	164 511	2 608 606 115
100	560	100	C1e	3	4	164 528	2 608 606 116
100	560	120	C1e	3	4	164 535	2 608 606 117
100	560	150	C1e	3	4	164 542	2 608 606 118
100	610	40	C1e	3	2	164 658	2 608 606 129
100	610	40	P0n	10	2	164 702	2 608 606 134
100	610	60	C1e	3	4	164 665	2 608 606 130
100	610	60	P0n	10	1	164 719	2 608 606 135
100	610	80	C1e	3	4	164 672	2 608 606 131
100	610	80	P0n	10	1	164 726	2 608 606 136
100	610	100	C1e	3	4	164 689	2 608 606 132
100	610	100	P0n	10	1	164 733	2 608 606 137
100	610	120	C1e	3	4	247 993	2 608 607 262
100	610	120	P0n	10	1	248 006	2 608 607 263
100	610	150	C1e	3	4	164 696	2 608 606 133
100	610	150	P0n	10	1	164 740	2 608 606 138
100	620	40	C1e	3	2	164 771	2 608 606 141
100	620	60	C1e	3	4	164 788	2 608 606 142
100	620	80	C1e	3	4	164 795	2 608 606 143
100	620	100	C1e	3	4	164 801	2 608 606 144
100	620	150	C1e	3	4	164 818	2 608 606 145
100	620	220	C1e	3	4	164 825	2 608 606 146
100	690	40	P0f	10	2	236 164	2 608 607 199
100	690	60	P0f	10	1	236 171	2 608 607 200
100	690	80	P0f	10	1	236 188	2 608 607 201
100	690	100	P0f	10	1	236 195	2 608 607 202
100	914	40	C1e	3	2	651 455	2 608 602 345
100	914	60	C1e	3	4	651 462	2 608 602 346
100	914	80	C1e	3	4	651 479	2 608 602 347
100	914	120	C1e	3	4	651 486	2 608 602 348


**BOSCH**