



verso mobile storage bench with full cupboard / 3 drawer cabinet / full cupboard. Featuring a robust, steel channel framework with integrated storage units 125mm diameter castors and a 30mm multiplex wood worktop. Delivered assembled. Equivalent cabinet - WxDxH:525/525/525x550x600mm. Drawer configuration: 1x 125, 2x 175mm with 100% extension slides (75kg U.D.L.) with two, reinforced 475 mm high doors. Finished in durable powder coat paint in RAL 7035 light grey / RAL 7016 anthracite grey. WxDxH: 1750x600x830mm.

Breite [mm]: 1750
Tiefe [mm]: 600
Höhe [mm]: 830
Bruttogewicht [kg]: 125.98
EAN-Code: 5039350103081
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Anthracite grey
Main RAL colour	RAL 7016
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	3
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125
Drawer height 2 [mm]	175

Drawer height 3 [mm]	175
----------------------	-----

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Beech Multiplex
Door type	Plain
Door height 1 [mm]	475