

Previously known as: PolarBear®74-045



Cut



Medium Duty

Lightweight, cut-resistant gloves providing excellent hand protection

- **Reinforced defenses:** HyFlex® 74-045 protective gloves offer a robust DSM Dyneema® core and high-strength outer wrap
- **Enhanced protection:** Ideal food safety gloves, they grant a high level of cut protection
- **Improved fit:** In addition, these cut-resistant safety gloves provide a comfortable fit, while delivering the protection of heavyweight gloves
- **Increased versatility:** These HyFlex® gloves may also be used as glove liners



Industries

- Food Processing

Applications

- Knifehand in processing areas
- Cleaning and changing slicer blades in delis and supermarkets

Previously known as: PolarBear®74-045

Key Features

- **DSM Dyneema® core and high-strength outer wrap:** Durable safety gloves
- **Excellent cut protection:** Ideal medium-duty gloves for handling food
- **Comfortable fit with heavyweight protection:** Added comfort and safety

Technologies



Performance Standards & Regulatory Compliance



1X4XC



254X

ANSI/ISEA 105-2024



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 74-045	Liner Material: Dyneema®, Fiber glass, Polyester Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	203 - 279 mm, 8-11 inches	12 pieces/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.