

CW-J10Ingress
protectionDrop
Resistance

Tumble Test

Barcode
Reader

NFC/RFID

NEW**ASSEMBLY & SERVICES IN FRANCE**

USED IN THE FIELD, VEHICLE, AND IN THE OFFICE

- MT6789, 8core ARM®
- Android 13
- Tested to MIL STD 810G, drop resistance 1.2m
- IP67, 100 times 1m "washing machine" test
- 12000mAh 3.8V battery, hot swappable
- 1000 nits, sunlight readable

OPTIONS & ACCESSORIES

- 4G LTE (optional)
- Barcode reader, NFC module
- Mobile docking station, dock office
- Handstrap, suitcase type handle





SPECIFICATIONS

SOFTWARE	Android 13	CAMERA	5MP front camera 13MP rear camera
DURABILITY	MIL-STD-810G (multiple drops 1.2 m) 26 times on each corner and each side with the same shelf in operation IP67 Tumble test 100 times x 1m Steel ball test (drop of 50cm on screen) Tempered Glass Screen Protector (Option)	WIRELESS	4G LTE GPS / GLONASS / GALILEO WIFI 802.11a b c, g, n Bluetooth® 5.0
CPU	MT6789, 8core ARM® Cortex-A55x6 + Cortex-A76x2, 2.2GHz	SECURITY	NFC reader (optional) RFID reader (optional)
RAM	8GB	POWER SUPPLY	Battery 3.8V, 12000mAh Battery life: up to 19 hours, hot swappable
STORAGE	256GB	SENSORS	2D barcode scanner (Option) 9-axis MEMS sensors (accelerometer, compass, gyroscope) Proximity sensor
DISPLAY	10.1" 1920x1200, IPS 1000 nits, sunlight readable	DIMENSIONS	275mm x 178mm x 18mm
AUDIO	1 microphone 1 built-in speakers	WEIGHT	1050 g
ENTRY	10-point multi-touch capacitive display, use mode with gloves and in the rain	ACCESSORIES AVAILABLE	Handstrap Suitcase handle Shoulder strap Mobile docking station Office station with battery charger Vehicle loader Rechargeable stylus Additive battery
INTERFACE	Station connector COM Port Power Supply Port DC 5V 3A 1 USB 3.1 Port (type A) 1 USB 3 Port (type C) RJ45 Gigabit Ethernet Port Audio Jack 3.5mm SD card slot SIM Slot	TEMPERATURE	Operating temperature from -20°C to 60°C Storage temperature from -25°C to 80°C