

VERSCHRAUBUNG SKV 16



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5167
Specification	VERSCHRAUBUNG SKV 16
HARTING eCatalogue	https://harting.com/09000005167

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	With strain relief

Technical characteristics

Wrench size	24
Degree of protection acc. to IEC 60529	IP68
Size	Pg 16
Width across corners	38 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	RAL 7032 (pebble grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)



Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)
------------------------------------	------------------------------

Commercial data

Packaging size	10
Net weight	19.25 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140002036
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431