

# UNILITE LED SWIVEL HEADED LANTERN

PS-L3  
/ L3RK



SEOUL

BEAMMASTER  
LENS

10  
HOURS  
RUNTIME

250  
METRE  
BEAM RANGE

300  
LUMENS  
OUTPUT

IPX4  
WATER  
RESISTANCE

- » 300 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Optical Beamaster lens for beam penetration
- » Swivel head rotation 135°
- » Easy screw battery replacement
- » Side charging point for use with PS-RB2LION
- » Impact resistant to 1m

**BATTERY** 1 x 6v PJ996 Lantern Battery (not inc.)

**WEIGHT** 449g (without battery)

**DIMENSION** 170 x 115 x 255mm



WALL BRACKET (INC.)



CARRY STRAP (INC.)

PS-L3RK

UNIVERSAL KIT

Rechargeable Kit including:

- » PS-L3 LED Lantern
- » PS-RB2LION 3.6v Li-ion 2600mAh Battery
- » DC-USB-KIT Charging Kit (inc UK, EU & AUS plugs)
- » 5v DC-USB Cable
- » 12v USB Car Adaptor
- » Carry Strap with Carabiners
- » Wall Mounting Bracket

