

Datasheet

Stock No: [102-3513](#)

Brushed DC Motor, 3000 rpm, 12 V, 250 W



Specifications:

Supply Voltage:	12 V
Motor Type:	Brushed
Duty Rating:	Cont
Power Rating:	250 W
Maximum Output Torque:	0.80 Nm
Output Speed:	3000 rpm
Shaft Diameter:	7.927 mm
Insulation Class:	F
Connection:	9.5 mm spade connector
Inertia (Kgm ²):	2.83×10^{-4}
Diameter:	90 mm
Length:	155 mm
Weight (Kg):	4.6
IP Protection:	IP44