

40101

Stainless Steel Scraper with Threaded Handle, 50 mm, Pink



Great for removing hard-to-reach sticky deposits and dried or burnt-on foods or ingredients, this Scraper features a stainless flex steel blade with protective rounded corners, a high-strength attachment, and a threaded handle that fits any Vikan colour-coded extension handle. While not intended for floor cleaning proper, this product can be used to remove lighter soils on floors.

Technical Data

Item Number	40101
Blade Thickness	1 mm
Material	Stainless Steel (AISI 303) Polypropylene Stainless Steel (AISI 301)
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	3150 Pcs.
Quantity Per Layer (Pallet)	150 Pcs.
Box Length	255 mm
Box Width	225 mm
Box Height	85 mm
Length/Depth	205 mm
Width	50 mm
Height	32 mm
Gross Weight	0,09 kg
Net Weight	0,08 kg
Cubik metre	0,0003 M3
Max. usage temperature (for food contact)	200 °C
Max usage temperature (non food contact)	200 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020401015
GTIN-14 Number (Box quantity)	15705020401012
Commodity Code	82159910
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.