PANDUIT

LWC19-H25-C

■ Part Number




LWC19-H25-C

- Holds wires, cables and tubing
 - Material: Nylon 6.6
 - Maximum Panel Thickness: .105"
 - Hole Diameter: .25"

Holds wires, cable and tubing and is available in 6 sizes with releasable latch. Adhesive backed and push mount styles available. Large mounting base for high bonding strength.

1 art rtarribor	21101011200
■ RoHS Compliancy Status	Compliant
■ Part Description	Push Barb Mount Latching Wire Clip
■ Product Type	Mounting Device
■ Material	Nylon 6.6
■ Color	Natural
■ Height (In.)	.41
■ Height (mm)	10.4
■ Length (In.)	.85
■ Length (mm)	21.6
■ Width (In.)	.51
■ Width (mm)	12.8
■ Environment	Indoors
■ Flammability Rating	UL94 V-2
■ Max. Bundle Diameter (In.)	.19
■ Max. Bundle Diameter (mm)	4.8
■ Max. Panel Thickness (In.)	.105
■ Max. Panel Thickness (mm)	2.7
Mounting Method	Push Barb
■ Panel Hole Diameter (In.)	.220
■ Panel Hole Diameter (mm)	5.6
■ Pricing Description	Latching Wire Clip, Push Mount, .19" (4.8mm) Bundle, NAT
■ Min. Order UOM	PC
■ Min. Order Qty.	100
■ BOM Qty. (# of Pkgs.)	


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT bs/100 pcs (g)/100 pcs	HOLE SIZE DIA. RANGE	PANEL THK. RANGE	
LWC19-H25	0.19	0.33	3/16"-1/4"	.025105	
	(4.8)	(150)	(5-6)	(0.5-3)	



1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.





							DIMENSIONS IN BRACKETS ARE METRIC [mm]						
					G00239EY_DC_02								
											ODUIT CORP.	TINLEY PARK, ILLINO	IS
										LWC19-H25 LATCHING WIRE CLIP			
										UNLESS OTHERWISE SPECIFIED, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:			
2	2-4-99	сөзм		CHANGED DIM. TO REF. DIM. UPDATED FILE NAME	GB0239EY	2				(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5° IN INCHES, THIRD ANGLE PROJE		CTION.	
1	12-15-97	Jad		.41 DIMENSION WAS .19, .86 DIMENSION WAS .85	GB0239EY	1				DRAWN BY CGSM	MAT'L:	scale 2X	
R	2/14/97	свям		INITIAL RELEASE	GB0239EY	R				DATE 2/14/97	NYLON 6/6	DRAWING NO.	DWG
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP		CHK'D		GB0239EY	SIZE