SHOEBOX-Enclosure

- 240 x 154 x 80mmm
- IP68 (Pressure Washer Proof)
- Tough ABS construction
- Wall Mount Lugs
- PCB Mounts on Lid and Base
- Supplied with Fixing Screws

Description

A general purpose ABS enclosure it has been lab tested to IP68.
The Lid and Base have PCB a multitude of fixing mounts, the case also has knock outs for five 20mm Cable Glands .

Part number	Description
ENC-SHOEBOX-KIT	Shoebox enclosure kit

Top Lid Detail



Top Lid Detail



Base Detail


KD01790
BACK CASING
PC / ABS
EXTERNAL - LIGHT SPARK
INTERNAL - LIGHT POLISH
IF IN DOUBT ASK
DO NOT SCALE
1:1
A1
1 of 2
SECTION D-D
SECTION B-B
SECTION A-A
NOTE(S):
- THIS DRAWING IS FOR REFERENCE ONLY.
- ALL RADIUS, UNLESS SPECIFIED, BROKEN TO R0.2mm.
- PLASTIC WEIGHT : 345g

Base Detail



ISS.	DESCRIPTION:	BY:	DATE:
06	GLAND CUTOUTS MODIFIED	NB	06-06-14
05	MODIFIED DUE TO TOOLING REQUESTS	NB	06-06-11
04	PRODUCTION ISSUE	NB	04-02-11

IF IN DOUBT ASK

Material: PC / ABS

Finish: EXTERNAL : LIGHT SPARK
INTERNAL : LIGHT POLISH

Drawing Standard To BS 308 / BS 3939

Drawing Title: BACK CASING

Drawing No: KD01790

DO NOT SCALE

Scale: 1:1

Paper Size: A2

Sheet No: 2 of 2

All Dimensions in MM (Unless Stated)

Drawn: NB 04-02-11

Checked: RF 04-02-11

Unspecified Tolerances
(Unless Stated Otherwise)
0 Decimal Place e.g. 10 = ±0.4
1 Decimal Place e.g. 10.0 = ±0.2
2 Decimal Place e.g. 10.00 = ±0.1
Angular Tolerance = ±0.5°
Apply Over Finish
(Except For Paint / Lacquer)

Wall Mounting template (not to scale)

All Dimensions in mm



Disclaimer:
Whilst the information in this document is believed to be correct at the time of issue, RF Solutions Ltd does not accept any liability whatsoever for its accuracy, adequacy or completeness. No express or implied warranty or representation is given relating to the information contained in this document. RF Solutions Ltd reserves the right to make changes and improvements to the product(s) described herein without notice. Buyers and other users should determine for themselves the suitability of any such information or products for their own particular requirements or specification(s). RF Solutions Ltd shall not be liable for any loss or damage caused as a result of user's own determination of how to deploy or use R F Solutions Ltd's products. Use of RF Solutions Ltd products or components in life support and/or safety applications is not authorised except with express written approval. No licences are created, implicitly or otherwise, under any of RF Solutions Ltd's intellectual property rights. Liability for loss or damage resulting or caused by reliance on the information contained herein or from the use of the product (including liability resulting from negligence or where RF Solutions Ltd was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict RF Solutions Ltd's liability for death or personal injury resulting from its negligence.

RF Solutions Ltd
William Alexander House, William Way, Burgess Hill, West Sussex, RH15 9AG
Sales: +44(0)1444 227 910 Tech Support: +44(0)1444 227909