



**Part Number :** [197084011](#)  
**Product Description :** PCB Tab Quick Disconnect,  
Male, for Wire, Box, Tab 4.75 x 0.81mm  
**Series Number :** 19708  
**Status :** Active  
**Product Category :** Quick Disconnects  
**Engineering Number :** 1640-3020



## Documents & Resources

### Drawings

[197084011\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-19708-001-001.pdf](#)

[PS-19902-013-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Quick Disconnects
Series	19708
Description	PCB Tab Quick Disconnect, Male, for Wire, Box, Tab 4.75 x 0.81mm
Product Name	PCB Tab
Type	Quick Disconnect
UPC	800753919846

### Agency

UL	E79133
----	--------

### Electrical

Voltage - Maximum	N/A
-------------------	-----

### Physical

Barrel Type	N/A
Gender	Male
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	None

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.350/g
Orientation	PCB Straight Tab
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	4.75mm
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A