



Cable D-Sub/end sleeve shie. 20x0.56 1m

connection cable shielded f. SIMATIC ET200 SP HA from 37-pole D-sub to bare ends with wire end sleeve labeled 20 channels L = 1 m, 0.56 mm²

Technical Product Detail Page	https://i.siemens.com/1P6ES7923-1BB00-0HD0
target system	SIMATIC ET 200SP HA
suitability for use	I/O modules
product type designation	Modular connection
product designation	Pre-assembled round cable
Operating data / header	
operating voltage / at DC	
• rated value	24 V
• maximum	60 V
ambient temperature	
• during operation	-30 ... +70 °C
• during storage	-30 ... +70 °C
General data / header	
suitability for interaction	
• input card PLC	No
• PLC output card	Yes
suitability for use	
• digital signal transmission	Yes
• analog signal transmission	No
Product properties, functions, components / general / header	
number of channels	10
design of cable	Round cable
wire length	1 m
number of poles	20
number of conductors / of connection cable	20
conductor cross section / rated value	0.56 mm ²
color / of cable sheath	Black
outer diameter / of cable sheath	10 mm
material / of the connection cable sheath	PVC
marking / of cores	label clip
design of the shield	braided shield
connector type	D-Sub connector
type of electrical connection / on enclosure	Female header
number of poles / at the 1st interface	37; control page
type of electrical connection / in the field	End sleeve
number of poles / at the 2nd interface	20; numbered
certificate of suitability	
• cULus approval	No
net weight	0.4 kg

