

# CORDED SPOT LAMP

## 777.SPOTPB

• 180° rotation

- Power Settings: **Low / Medium / High**
- Lumens: **1500 / 2500 / 5000**
- Detachable Base with powerful **magnets** for hands-free use
- **Handles** for carrying and easy adjusting
- **180°** Rotation
- **360°** Swivel
- Corded
- IP Rating: **IP67**
- IK Rating: **IK07**
- **UNIQUE DESIGN**
- CRI: **85** keep a natural color



• **Magnetic base**

- Optional Tri-Pod Stand 779.TRIPODPB

- Dimensions (L x h x w) : 320 X 150 X 260 mm
- Cable length: 5 m
- Weight : 3,0 kg

