

BM ID-MAG40 - Magazine



1044357
<https://www.phoenixcontact.com/gb/products/1044357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Infeed magazine for accommodating a maxi. of 40 UniCard sheets



Commercial data

Item number	1044357
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG121Z
Product key	BG121Z
Catalog page	Page 33 (C-3-2019)
GTIN	4055626622583
Weight per piece (including packing)	1,090 g
Weight per piece (excluding packing)	1,076 g
Customs tariff number	84439990
Country of origin	DE

BM ID-MAG40 - Magazine

1044357

<https://www.phoenixcontact.com/gb/products/1044357>



Technical data

Product properties

Product type	Magazine
--------------	----------

Material specifications

RoHS compliant	yes
----------------	-----

Environmental and real-life conditions

Ambient conditions	
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Classifications

ECLASS

ECLASS-13.0	19140192
-------------	----------

ETIM

ETIM 9.0	EC001675
----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk