

HP2051F

No Load Speed	H: 0 - 2900 / L: 0 - 1200 rpm
Blows per minute	H: 0-58000/ L: -2400 bpm
Input wattage	720 w
Vibration: Drilling	2.5 m/sec ²
Vibration: Hammer Drilling	13 m/sec ²
Vibration K factor	3 m/sec ²
Noise sound pressure	97 dB(A)
Noise sound power	108 dB(A)
Noise K factor	3 dB(A)
Net weight	2.3 kg



STANDARD EQUIPMENT: 824650-5 CARRYING CASES FOR MAINS MACHINES - PLASTIC

- Built-in job light
- Forward/reverse rotation
- 2 mechanical gears.
- Torque limiter: The drill stops when the bit hits against reinforcements.
- Variable speed - ideal for various materials
- Anti Vibration System
- Double Insulation
- Keyless Chuck