

0 601 37B 270 – GEX 40-150


Material number	0 601 37B 270
EAN	4059952528816
1 x sanding sheet M480, Best for Wood + Paint, 120 available separately as set of 5: 2 608 621 164	✓
L-BOXX238N 1 600 A01 2G2	✓



Technical data

Technical data

Sanding pad diameter	150 mm
No-load speed	5,500 – 12,000 rpm
Orbital stroke rate	11,000 – 24,000 opm
Eccentricity	2,00 mm
Sanding sheet / disc attachment	Hook-and-loop fastening
Rated input power	400 W
Weight	2,4 kg
Tool dimensions (length)	409 mm
Tool dimensions (height)	197 mm
Orbit diameter	4,0 mm
Packaging dimensions (width x length x height)	360 x 443 x 240 mm
Voltage, electrical	240 V
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level dB(A); Sound power level dB(A). Uncertainty K= dB.



Sales information

Positioning

- The high-performance corded random orbit sander for professional finishes in the 150-mm category

User benefit

- Housing with a decoupled sanding unit for consistent contact pressure, enabling high-quality surface results
- Unique vibration damping produces very low vibrations for continuous work
- Speed preselection option enables use in multi-material applications