

6.00865.50

SBE 900 Impuls
 4007430193872

900 Watt Electronic Two-Speed Impact Drill SBE 900 Impuls



- Selectable impuls mode for precise driving of screws and comfortable drilling
- Vario-Constamatic (VC) full-wave electronics for infinitely variable speed change. Under load the speed remains almost constant.
- Thumbwheel for preselection of speed
- Thumbwheel for setting the torque
- Die cast aluminium gear housing for optimum heat dissipation and stability
- Maximum performance even in anti-clockwise rotation due to rotating carbon brush bridge
- Two-speed gear unit
- robust Metabo Marathon Motor for up to 5 times increased service life for extra long service life
- Metabo S-automatic torque limiting clutch: to limit any sudden reverse torque that can occur if tools jam or get caught.
- Clockwise and anticlockwise rotation
- Spindle with hexagon recess for screwdriver bits
- Rubber-coated handle: vibration-reduced, comfortable and safe
- Twist- and slip-proof additional handle for even more work safety
- Cable-protecting ball spout for best freedom of motion when working
- Auto-stop carbon brushes to protect the motor

Comparative technical values

Maximum torque	38 Nm/14 Nm
- Drill diameter in	
- Concrete	20 mm
- Steel	13 mm/8 mm
- Soft wood	40 mm/25 mm
Idle revolution	0 - 1.000 / 0 - 3.100 /min
Rated input power	900 W
Output power	550 W
Revolutions at rated load	800/2.300 /min
Maximum impact rate	59.000 /min
Collar diameter	43 mm
Drill spindle thread	1/2" -20 UNF
Chuck adapter	1,5 - 13 mm
Drill spindle with hexagonal recess	1/4" (6,35 mm)
Weight (without power cable)	2,7 kg

Scope of delivery

Futuro Plus quick-action keyless chuck, Rubber-coated side handle, Drilling depth guide, Plastic carry case