

FR28 - Bizflame Work FR Coverall

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre, 280g

Outer Carton: 12

Product information

Constructed using a lighter weight highly innovative flame resistant BizFlame Work fabric.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)
EN ISO 11611 Class 2 (A1+A2)
EN 1149 -5
EN 17353 Type B2



Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Two tier knee pad pockets allowing two positioning options
- Side access openings
- Sleeve pocket
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access

FR28 - Bizflame Work FR Coverall Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/13017-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR28GRRS	Grey	43.0	28.0	46.0	1.2800	0.0554	5036108284009	15036108774194
FR28GRRM	Grey	43.0	28.0	46.0	1.2600	0.0554	5036108283996	15036108774187
FR28GRRL	Grey	43.0	28.0	46.0	1.4300	0.0554	5036108283989	15036108774170
FR28GRRXL	Grey	43.0	28.0	46.0	1.4400	0.0554	5036108284016	15036108774200
FR28GRRXXL	Grey	43.0	28.0	46.0	1.5000	0.0554	5036108284023	15036108774217