

Datasheet

RS Pro Non-Fused Terminal Block, 1 Way/Pole, Screw Terminals, 35 mm², PC, 450 V

RS Stock No: **868-0770**



Product Details

RS Pro non-fused terminal block is designed for termination or the joining of cable ends. This 1-way polycarbonate terminal block with 35-mm² wire, features screw termination. The panel mount terminal block with brass contact, has a voltage rating of 450 V. This terminal block meets EN 60998-1: 2004 and EN 60998-2-1: 2004 standards.

Features and Benefits

- Transparent blue polycarbonate housing UL 94 - V0
- Funnel cable entry
- Screw clamp
- Peak operational temperature of 85°C
- Brass clamp
- Screw material: galvanised steel
- High mechanical resistance with good electrical characteristics

**Specifications:**

| | |
|-------------------------------|---|
| Contact Material | Brass |
| Enclosed | Yes |
| Material | PC Housing |
| Maximum Operating Temperature | +85°C |
| Mounting Type | Panel Mount |
| Number of Ways | 1 |
| Termination Method | Screw |
| Voltage Rating | 450 V |
| Wire Size | 35 mm ² |
| Colour | Transparent Blue |
| Standards Met | RoHS, UL 94V-0, EN 60998-1:2004, EN 60998-2-1:2004 |