

Datasheet

## RS Pro Stainless Steel Countersunk Head Machine Screws, M8 x 45mm

RS Stock No: **914-1936**



### Product Details

RS Pro machine screw measuring M8 x 45 mm, is made of type 316 S16 A4 grade 18//8 stainless steel, which has higher level of corrosion resistance than A2 stainless steel. The countersunk head screw can be used at up to 300°C. The slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

### Features and Benefits

- A4 grade 18/8 stainless steel (Type 316 S16) construction
- Higher level of corrosion resistance than A2 S/S
- Suitable for use up to 300°C
- Suitable for use in most food, medical, chemical, construction and electronic applications

**Specifications:**

Drive Type	Slot
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	45 mm
Stainless Steel Type	316 (A4)
Thread Pitch	1.25
Thread Size (Metric)	M8
Head Diameter	15.37 to 15.8 mm
Head Height	4.65 mm
Slot Depth	1.8 to 2.3 mm
Slot Width	2 mm
Specification	DIN 963