

VARTA Aluminium Light F20 Pro 2AA with Batt.



Elegant flashlight with black anodized aluminium housing and silver ring in matte finish with 3 light modes, high lumen output and long runtimes.



Information

- Precision focus (Infinitely focusable light beam spot-to-flood)
- Anodized aluminium body
- Textured housing surface for maximum grip
- 3 light modes: high, low, strobe
- Shock proof (1 m)
- Rear mechanical switch
- High performance LED

Article Details

Ordernumber	16607 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	70.00 m
Runtime	35 h
Total light output	250 lm
Product Diameter mm	26.20
Product Length / Depth mm	164.10
Product Weight g	74.80

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 056446	100.00	25.00	230.00	0.14
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	6	40 08496 056699	245.00	146.00	115.00	0.95
PAL (Pallet)	1296	40 08496 056712	800.00	1,200.00	1,185.00	225.72
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
9	24		216		6	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

