

Features

- Medium Duty
- Stainless Steel
- Brake
- Industrial castor
- Rotation Swivel
- Fixing Hole
- Polyamide 6
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0730086



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Polyamide 6 wheel. Hub on plain bore. In pressed stainless steel AISI 304, turning on double rim of balls in stainless steel AISI 420. Assembled with self-locking nut.

General Specifications

Rotation	Swivel
Weight Class	Medium Duty
Load Capacity (Kg)	300
Load Capacity / 4pcs (Kg)	1200
Tyre Material	Polyamide 6
Hub Material	Polyamide 6
Bracket Material	Pressed Stainless Steel
Includes Brake	Yes
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-25° to 85°
--	-------------

160x40	55	194	16	300	380

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	160
Wheel / Tread Width (mm)	40
Overall Height (mm)	194
Number of Fixing Holes	1
Fixing Hole Size (mm)	16
Hub Bearing Type	Roller Bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	97
Levelling Extent (mm)	
Offset (mm)	55
Castor Weight (Kg)	1.650

Fixing Centres Specifications

Fixing Centres (mm)	
Fixing Centres Length (mm)	
Fixing Centres Width (mm)	

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	
Fixing Plate Length (mm)	
Fixing Plate Width (mm)	