



Module pour configuration de la durée de rampe, protection des moteurs, fonction borne de commande pour démarreur à vitesse variable DE



Référence **DXE-EXT-SET**
 N° de catalogue **174621**
 Alternate Catalog **DXE-EXT-SET**
 No.

Gamme de livraison

Description		avec sélecteur pour temp de ramp et mode de fonctionnement avec potentiomètre pour protection des moteurs et fréquence fixe
Utilisation avec		DE1, DE11
Raccordement		Module enfichable (face avant)

Vérification de la conception selon IEC/EN 61439

Caractéristiques techniques pour la vérification de la conception		
Température d'emploi min.	°C	-10
Température d'emploi max.	°C	50

Caractéristiques techniques ETIM 7.0

Commutateurs basse tension (EG000017) / Accessoires pour convertisseur de fréquence (EC002025)		
Electricité, Electronique, Automatisation et Commande / Entraînement électrique / Variateur de vitesse (convertisseur de fréquence) / Static frequency converter (accessory) (ecl@ss10.0.1-27-02-31-92 [AFR303003])		
type d'accessoire		autre

Homologations

Product Standards		UL 508C; CSA-C22.2 No. 274; IEC/EN61800-3; IEC/EN61800-5; CE marking
UL File No.		E172143
UL Category Control No.		NMMS, NMMS7
CSA File No.		UL report applies to both US and Canada
North America Certification		UL recognized, certified by UL for use in Canada
Specially designed for North America		No
Suitable for		Branch circuits

Encombrements



