







8790 HMB Zyklus $\frac{3}{8}$ " socket



Application: Hexagon headed bolts, screws and nuts

Design: Manual and (non-impact) machine applications, ball intercept ring, knurls at base for precision handling in manual operations, chrome vanadium, brushed chrome-plated finish
Take it easy toolfinder: Colour coding to enable the desired socket to be easily located.

						
	mm	mm	mm	mm	mm	mm
05003551001	6,0		29,0	10,5	18,0	12,0
05003552001	7,0		29,0	11,0	18,0	12,0
05003553001	8,0		29,0	12,2	18,0	12,0
05003554001	9,0		29,0	13,5	18,0	12,0
05003555001	10,0		29,0	14,5	18,0	12,0
05003556001	11,0		29,0	16,0	18,0	12,0
05003557001	12,0		29,0	17,0	18,0	12,0
05003558001	13,0		29,0	18,5	20,0	12,0
05003559001	14,0		29,0	19,5	22,0	12,0
05003560001	15,0		29,0	21,0	24,0	12,0
05003561001	16,0		30,0	22,0	24,0	12,0
05003562001	17,0		30,0	23,5	24,0	12,0
05003563001	18,0		30,0	24,5	24,0	18,0
05003564001	19,0		30,0	26,0	24,0	18,0
05003565001	20,0		30,0	28,0	25,0	18,0
05003566001	21,0		30,0	28,0	25,0	18,0
05003567001	22,0		30,0	32,0	25,0	18,0
05003568001	24,0		32,0	32,0	25,0	20,0
05003569001		$\frac{1}{4}$ "	29,0	11,0	18,0	12,0
05003570001		$\frac{5}{16}$ "	29,0	12,2	18,0	12,0
05003571001		$\frac{11}{32}$ "	29,0	13,5	18,0	12,0
05003572001		$\frac{3}{8}$ "	29,0	14,5	18,0	12,0
05003573001		$\frac{7}{16}$ "	29,0	16,0	18,0	12,0
05003574001		$\frac{1}{2}$ "	29,0	18,5	20,0	12,0
05003575001		$\frac{9}{16}$ "	29,0	19,5	22,0	12,0
05003576001		$\frac{5}{8}$ "	30,0	22,0	24,0	12,0
05003577001		$\frac{11}{16}$ "	30,0	23,0	24,0	18,0
05003578001		$\frac{3}{4}$ "	30,0	26,0	24,0	18,0
05003579001		$\frac{13}{16}$ "	30,0	28,0	25,0	18,0
05003580001		$\frac{7}{8}$ "	30,0	32,0	25,0	18,0