

Datasheet

Steel Combination Pliers

RS Stock number [161-164](#)



Description:

Constructed from high grade steel with mirror polish and slip guard
Two component handle for ease of use
VDE tested and confirms to IEC 900 1000V
Made in Germany
For soft and hard wire (H)
Long precision cutting edges, knurled jaws for flat and serrated pipe hole for round pieces
With facet for a better access
Cutting edge with external bevel
Gripping surface serrated

Specifications:

Cutting Capacity:	Piano Wire – 3 mm
Cutting Capacity (Screws):	M3.5
Material:	Steel
Overall Length:	200 mm
VDE / 1000V Approved:	Yes