

562577

Shovel, D Grip, 327 x 271 x
50 mm, 1040 mm, Lime



This Shovel features a one-piece construction that eliminates areas where bacteria can gather. Its smooth surface allows for easy cleaning, which makes it ideal for moving food ingredients or large quantities of food waste. This product is ideal for shovelling from eg. container to container.

Technical Data

Item Number	562577
Shovel Blade Size, L x W x H	327 x 271 x 50 mm
Material	Polypropylene
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	75 Pcs.
Quantity Per Layer (Pallet)	15 Pcs.
Box Length	1190 mm
Box Width	265 mm
Box Height	365 mm
Length/Depth	1040 mm
Width	271 mm
Height	120 mm
Gross Weight	1,46 kg
Net Weight	1,26 kg
Cubik metre	0,0338 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature ³	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "5", Polypropylene (PP)	Yes
GTIN-13 Number	5705022014169
GTIN-14 Number (Box quantity)	15705028014191
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.