

Technical Characteristics

| | |
|--------------------------|---|
| Bezel Material | Chromium Plated Metal |
| Ampere Rating | 10A |
| Approvals | UL Listed File Number E42259 CCN NKCR - CSA Certified File Number LR25490 Class 3211 03 - CE Marked |
| Catalog Reference Number | 9001CT0001 |
| Contact Configuration | 1 N.O./1 N.C. |
| Contact Material | Silver Alloy |
| Enclosure Type | Water tight, Dust tight and Oil tight (Indoor/Outdoor) |
| Enclosure Rating | NEMA 4/13 |
| Head Type | Round |
| Cam Type | Cam B |
| Knob Color | Black |
| Knob Type | Standard |
| Maximum Voltage Rating | 600V |
| Mounting Type | Panel |
| Mounting Position | All |
| Number of Operators | 1 |
| Number of Positions | 3 |
| Operator Action | Maintained |
| Operator Type | Non-Illuminated |
| Terminal Type | Screw Clamp |
| Size | 30mm |
| Type | K |
| Utilization Category | AC15 - DC13 |

Shipping and Ordering

| | |
|-------------------|---|
| Category | 21426 - Push Buttons, 30 mm, Metal, Round, Type K |
| Discount Schedule | CP1 |
| Article Number | 785901899105 |
| Package Quantity | 1 |
| Weight | 0.5 lbs. |
| Availability Code | Non-Stock Item: This item is not normally stocked in our distribution facility. |
| Returnability | Y |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.