

Datasheet

LED Brick Light



Description

This fitting is ideal for installation within solid brick wall, in place of a brick. Ideal for amenity and walkway lighting around a building, or for use in perimeter brick walls and driveways.

Features

- Energy efficient replacement for CFL and incandescent fittings
- Designed to be installed in a wall in place of a brick
- Polycarbonate body with stainless steel bezel
- Daylight (6000K) colour temperature
- Integral driver
- Rated life of 25,000 hours
- 2 year guarantee

Range

LED 2W Brick Light 7959394

Dimensions (mm)

	Length	Height	Depth
7959394	198mm	74mm	65mm

Technical Specification

Voltage	230V ~ 50Hz
Driver	Integral
Lamp	5mm LEDs
Lamp colour temp.	6000K
Wattage	2W
Lumen output	120lm
Lumen per Watt	60lm/W
CRI	Ra 79.9
Beam angle	120°
IP Rating	IP65

Standards

- BS EN 60598-1: 2008
- BS EN 55015: 2006+A1: 2007+A2: 2009
- BS EN 61000-3-2: 2006+A1: 2009+A2: 2009
- BS EN 61547: 2009