

### FR21 - Bizflame Work Lightweight FR

#### Coverall

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 210g

**Outer Carton:** 14



#### Product information

This coverall is perfect for the extra warm weather demands of the offshore industry. Constructed with a lighter weight highly innovative flame-resistant twill fabric.

##### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

##### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 11612 (A1+A2, B1, C1, E2,F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV = 9.1cal/cm<sup>2</sup>)

#### Features

- Lightweight for enhanced wearer comfort
- Protection against radiant, convective and contact heat
- Rule pocket
- Two back patch pockets
- Durable, strong and long lasting brass zip
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Sleeve pocket
- 10 pockets for ample storage
- Two tier knee pad pockets allowing two positioning options
- Two-way zip for quick and easy access

### FR21 - Bizflame Work Lightweight FR Coverall Commodity Code: 6211321000

#### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
Bracetown Business Park  
D15 YN2P, Ireland  
Cert No: 2777/12375-06/E00-00

#### Wash Care



#### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR21ORTM	Orange Tall	43.0	28.0	58.0	1.1550	0.0698	5036108311170	25036108799712
FR21ORTL	Orange Tall	43.0	28.0	58.0	1.1930	0.0698	5036108311163	25036108799705
FR21ORTXL	Orange Tall	43.0	28.0	58.0	1.2450	0.0698	5036108311187	25036108799729
FR21ORTXXL	Orange Tall	43.0	28.0	58.0	1.2700	0.0698	5036108311194	25036108799736