

Features

- Flexible and durable H05VVF3G1.00- pvc cable
- European plug VII-CEE (7) -Right Angled
- Untermated end jacket stripped 40mm
- Fully moulded plug for strength and durability
- 5.00m Length

RS PRO 5.00m Power cable Untermated to VII CEE (7) 10A 250 V

RS Stock No.: 0857458



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- From RS PRO a high quality and durable power supply cord suitable for various applications. Supplied with fully moulded plug with double earth contacts combined with 1.00mm sq. harmonised cable and unterminated end jacket strip 40mm. These cables have an unterminated end meaning they can be hard wired to any suitable connector or hard wired direct to appliance.

General Specifications

Connector A	Stripped end Outer jacket 40mm
Connector B	CEE (7) VII Male – Right angled
Sheath Colour	WHITE
Material	PVC
Applications	DIY and home improvements, Maintenance work, Household Entertainment (TVs, Satellite boxes, routers etc.) Industrial machines and equipment Office desks (monitors, computers, phones) Any Electrical device needed to be powered by mains.

Mechanical Specifications

Length	5.00m
--------	-------

Electrical Specifications

Power Cord Rating	10 A - 250V
Visual Inspection	100%
Electrical Test	100%
High pot test wire to wire	3kVac for 2 sec.
Continuity test	25Aac to grounding / 20A to line and neutral
Polarity test	yes
Skin high pot test	6kVac line to skin


Protection Category

	Eu-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (RoHS-Compliant)

Approvals

Stripped end	N/A
VII CEE (7)	VDE, OVE, CEBEC, KEMA, S, D, N, FI, LCIE, IMQ, K
Cable	Harmonised <HAR>

5000 +/- 50



All Dimensions in mm