

FEATURES

- 50 Ω impedance
- Operating frequency is 1GHz
- BNC plug to BNC 2 x socket RF adapter
- Nickel plated body and gold plated centre contact

RS PRO BNC plug to BNC 2 x socket

RS Stock No.: 217-7791



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

BNC plug to BNC 2 x socket RF adapter features bayonet couplings, nickel plated body and gold plated centre contact. It has 50 Ω impedance. This adapter is suitable for a variety of applications including video signalling and test equipment.

Suitable for a variety of applications including video signalling and test equipment.

General Specifications

Type of coaxial connector	BNC plug to BNC 2 x socket
Body Plating	Nickel
Termination method	Cable
Contact Material	Brass
Contact Plating	Nickel
Gender A	Plug
Gender B	Socket
Mounting type	Panel mount

Electrical Specifications

Temperature Range	-20° ~ +60°
Characteristic Impedance	50 Ω
Frequency Range	0~1GHz
Working Voltage	335V
Insulation Resistance	$\geq 1000M\Omega$
Medium Pressure	1000V(rms)
VSWR	≤ 1.35
Working Life	500Cycles

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5464948	RS PRO	RF Adapter	50Ω impedance	Operating frequency is 11GHz	

