KÄRCHER PIPE CLEANING HOSE (NW 6, 20 M)



Length: 20 m

Nominal width: 6

Temperature: up to max. $60^{\circ}\ \text{C}$

Pressure: 120 bar

KÄRCHER HIGH-PRESSURE HOSE (10 M, 315 BAR, NW 8)



For extending the operating range with the high-pressure cleaner

Length: 10 m

Nominal width: 8

maximum pressure: 315 bar

Connections: 2 x M 22 x 1,5

KÄRCHER PIPE CLEANING NOZZLE



3 x 30° backwards

Ø 30 mm

Nozzle size: 50