SIEMENS

Data sheet 3NC2240-0MK

Figure similar

SITOR cylindrical fuse link, 22x58 mm, 40 A, gR, Un AC: 690 V, Un DC: 440 V

Model	
product brand name	SENTRON
product designation	SITOR cylindrical fuse link
General technical data	
operating class of the fuse link	gR
type of voltage of the operating voltage	AC
supply voltage at DC	440 V
Main circuit	
operational current rated value	40 A
Product details	
product component striker	No
Mechanical Design	
mounting position	Any, preferably vertical
net weight	57 g

Approvals Certificates

General Product Approval	other	Environment
CE EG-Konf. UKCA UL EAC	Confirmation	Environmental Confirmations

Environment

Environmental Confirmations

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2240-0MK
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3NC2240-0MK
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2240-0MK
CAx-Online-Generator

Subject to change without notice
© Copyright Siemens

http://www.siemens.com/cax
Tender specifications
http://www.siemens.com/specifications



last modified: 4/11/2025

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens