







THREE KINDS OF DIFFERENT POCKETS AS 1 SET
USED FOR 7P ONLY



TYPE "B"



△ PEELING RESISTANCE : 0.196N-0.686N (20gf-70gf)
SPEED : 300mm/min

CUSTOMER DRAWING


NATURAL	WITH	B	20.2	44	24	500	9	1-292173-9	
		B	20.2	44	22		8	1-	 -8
		B	14.2	32	20		7	1-	-7
		B	14.2	32	18		6	1-	-6
		B	11.5	24	16		5	1-	-5
		B			14		4	1-	-4
		A			12		3	1-	-3
		A	11.5	24	10		2	1-	-2
BLACK		B	20.2	44	24		9	0-	-9
		B	20.2	44	22		8	0-	-8
		B	14.2	32	20		7	0-	-7
		B	14.2	32	18		6	0-	-6
		B	11.5	24	16		5	0-	-5
		B			14		4	0-	-4
		A			12		3	0-	-3
	WITH	A	11.5	24	10	500	2	0-292173-2	
COLOR	PLATE	TYPE OF ROSS	C	B	A	QTY/REFL	Pos	TAPING	P/N



ON TAPING (EMBOSS)
TE CT CONNECTOR POST HEADER ASS'Y
(BOX-H SMT TYPE W/BOSS & TAIL)

SCALE	$\frac{1}{4}$	SHEET	1 OF 6	REV	C2
-------	---------------	-------	--------	-----	----

[illegible]



FOR 7P ONLY

THREE KINDS OF DIFFERENT POCKETS AS 1 SET
USED FOR 7P ONLY




Figure 1 is a cross-sectional diagram of a reel assembly. The diagram shows a central reel hub with a winding drum and a flange. Dimensions are indicated: 5.5 and 5.3 for the flange thickness, 0.5 for the hub thickness, and 6.1 for the total width. A large arrow points to the left, labeled "TOP OF REEL".

Fig-1




Fig-2

△ PEELING RESISTANCE : 0.196N-0.686N (20gf-70gf)
SPEED : 300mm/min

CUSTOMER DRAWING

A3 00779 C-292173

SCALE $\frac{1}{2}$

SHEET 2 OF 6

REV C2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


- SEE SHEET 1

-


-

-


LAYOUT FOR 292173-X,1-292173-X



5 POS. & ABOVE POS.




3 POS.



2 POS.

RECOMMENDED P.C. BOARD LAYOUT
(P.C.B THK:0.8mm MIN)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	± -

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

SMT TYPE POST HDR ASS'Y (H)
WITH BOSS & TAIL TYPE
(TE CT CONN. 2mm PITCH)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-292173

SCALE 5:1

SHEET 4 OF 6

REV C2

