

Datasheet

Vertical Switched Interlocked Wall-Mount Socket-Outlet

Stock No:
2144264



Image for reference only


Technical Characteristics

Rated Current:	32
Rated Voltage	400
Poles	4P (3P+T)
Clock Position	6h
Rated Frequency	50/60Hz
Insulating Resistance	>10MΩ@500Vdc
Dielectric Stength	2,5kV 60s
IP Protection Degree	IP67 (IEC / EN 60529)
Operating Temperature	-5°C/ 40°C
Glow Wire Test	850°C live parts supports /650°C other parts
Material	Housing: PA6/ABS
Product Standard	IEC/EN 60309-1, IEC/EN 60309-2, IEC/EN 60309-4

Datasheet

Vertical Switched Interlocked Wall-Mount Socket-Outlet

Stock No: 26004-RSC



Dimensions in mm

A	B	C	D	E	F	G	ØK
90	180	140	55	165	60	92	-