

### **FEATURES**

- Stainless steel superior corrosion resistance
- Suited to higher pressure and temperature applications
- Investment casting
- Blow-out proof stem
  protects the operator
- Anti-static device (option)

# RS PRO Stainless Steel High Pressure Ball Valve 1-1/2 in BSPP 2 Way

RS Stock No.: 499-2830



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

Introducing the RS PRO general purpose manual ball valve designed for industrial applications. Manual ball valves are used to operate shut off valves which control water flow and pressure.

Available in a variety of sizes:

499-2789 - 1/4 inch BSPP F-F

499-2795 - 1/2 inch BSPP F-F

499-2802 - 3/4 inch BSPP F-F

499-2818 - 1 inch BSPP F-F

499-2824 - 1-1/4 inch BSPP F-F

499-2830 - 1-1/2 inch BSPP F-F

499-2846 - 2 inch BSPP F-F

#### **General Specifications**

Threaded Connection	1-1/2 in BSPP			
Attachment Type	Threaded			
Body Material	ASTM A351-CF8M			
Thread Size	1-1/2in			
Safe For Use With	Gas, Oil, Water			
Ball Material	ASTM A351-CF8M			
Thread Standard	BSPP			
Handle Material	Stainless Steel			
Туре	2 Way			
Application	Heating systems; Water treatment; Liquid flow control			

#### **Mechanical Specifications**

Connection Size	38.1mm
Torque	7.4Nm
Weight	0.9kg



## **Operation Environment Specifications**

Working Temperature	-20°C to 200°C		
Maximum Working Pressure	68 bar		

## **Approvals**

Compliance/Certifications	ISO-5211
















	ITEM	PAR	RTS		MATERIAL			
	1	BOI	BODY			ASTM A351-CF8M		
	2	RETA	INER		ASTM A	ASTM A351-CF8M		
	3	BODY	BODY SEAL			PTFE		
	4	BA	LL		ASTM A351-CF8M			
	5	BALL	SEAT		PTFE / RTFE			
	6	STE	STEM		ASTM A276-316			
	7	FLAT WASH			AISI 304			
	8	SPRING V	SPRING WASHER		AISI 304			
	9	STEM	STEM NUT		AISI 304			
	10	THRUST \	WASHER		PTFE			
	11	PACK	ING		PTFE			
12		HANDLE		STAINLESS STEEL				
					STAINLESS STEEL			
13		LATCH	LATCH LOCK		STAINLESS STEEL			
	14	HANDLE SLEEVE		PVC				
DN d 40 25	L L1 83 40.5	H H1 63.2 46.5	W 160	S 8	Torque (N-m 7.4	) Weight (kg) 0.9		