



## MEGA S 60-PP1

Bolt-On Fuse, Small, 60A

### Product Properties:

Explosion-proof	No
Release characteristic	Time-lag (T)
Rated voltage	32 V
Optical defect indication	Yes
Type of current	DC
Colour code	Black
Nominal voltage DC	32 V
Max. continuous voltage DC	32 V
Number of fuses	1 .
Model	Other
Max. current (I <sub>max</sub> )	60 A
Nominal current	60 A
Fuse type	Mega S

### Dimensions:

Width	40.8 mm
MOQ	10 .
Unit	pck
Rated voltage	32 V
Mounting holes	M6
Centre-to-centre distance of connections	30 mm
Thickness	8.3 mm
Length	12.1 mm

### Approvals:

## **Compliance:**

<b>Conflict Minerals</b>	Contain "Tin"
<b>REACH</b>	No SVHC (Latest. 04 Feb 2026)
<b>RoHS</b>	RoHS 3 (2015/863)
<b>SCIP</b>	Not Applicable

## **Other information:**

<b>ETIM-Class</b>	EC004122 - Strip fuse
<b>ETIM-Release</b>	DYNAMIC
<b>Trademark</b>	NECORE
<b>Product Group</b>	Bolt-on / Strip fuses - Pin-pac
<b>Search Description</b>	MIDI
<b>Alternative SKU</b>	MEGAS60-PP1

## **Logistic information:**

<b>Barcode</b>	733117610358
<b>Country of origin</b>	JP
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	10 .
<b>Stock code</b>	MEGA S 60-PP1
<b>Taric code</b>	85361050
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.