

S.306-350DSLS 306D.SLS - Click wrenches without accessories**Description :**

- Tool equipped with a FACOM SLS attachment solution, preventing any risk of accidental falls.
- FACOM has adopted the clevis solution for particularly heavy and/or large tools (32 - 41 mm wrenches).
- Factory accuracy: $\pm 2\%$ except: R.306-25DSLS.
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories:
 - End fitting: 9 x 12 or 14 x 18 mm.
 - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in plastic box.

L [mm]: 725

Attachment: 14 x 18

Box: BP.D3

Capacity [N.m]: 70 - 350

Graduation [N.m]: 2,00

[kg]: 1,830
