

Hybridcbl. Papst CSD_LAiO2 HD 3,0m



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 720 0053 0300
Siemens part number	HRT:6172530300
Specification	Hybridcbl. Papst CSD_LAiO2 HD 3,0m
HARTING eCatalogue	https://harting.com/618872000530300

Identification

Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 Female 12 + 3 poles
Connector 2	wire end ferrules
Type of cable	Copper cable (round)
Description of the cable	Oil resistant Halogen-free Silicone-free
Features	Highly flexible Drag chain compatible

Version

Cable length	3 m
Core structure	3x 1.5 mm ² + 2x 0.34 mm ² + 2x 2x 0.22 mm ²
Field of application	for hybrid function

Termination data

Nominal voltage	60 V DC
-----------------	---------

Technical characteristics

Limiting temperature	-20 ... +80 °C unmoved -20 ... +80 °C moved
----------------------	--



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black

Specifications and approvals

Specifications	IEC 60332-1 Flame retardancy
----------------	------------------------------

Commercial data

Packaging size	2
Net weight	496.5 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140274594
eCl@ss	27060490 Ready-made low-voltage line (unspecified)
ETIM	EC002587
UNSPSC 24.0	26121629