



Datasheet

4030.7126RN – Flat speaker cable 2 x 1.50 mm²

EN

Conductor :

- Stranded
- Section : 1.50 mm²



Outer Jacket :

- Insulation : PVC
- Colours coding : red / black
- Ø : 2,60 x 5,20 mm

PRODUCT INFORMATION

Application

- Wiring all types of sound systems
- For fixed and mobile installations
- Conductor identification by colour

Electrical Properties

- Operating tension : < **900 V**
- Test tension : > **2500 V**
- Electrical resistance at 20°C : **18.1 Ω/km**

Characteristics

- Temperature range : **Static use** : - 25°C → + 70°C
 - **Mobile use** : - 5°C → + 70°C
- Minimum bending radius : **8 x Ø**
- Conform to **RoHS directive**
- Packaging : **100 m**